


Toolholder form B5 radial right-hand, long, Shank Ø d1: 30mm

Order data

Order number	319070 30
GTIN	4045197955005
Item class	32V

Description
Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

h_1	20 mm
h_5	38 mm
l_2	40 mm
h_2	29 mm
b_1	100 mm
h_6	28 mm
b_2	65 mm

Data sheet

Colour code for VDI shanks	VDI 30
Shank Ø D ₁	30 mm
l ₁	22 mm
Shape	B
Type of product	VDI tool arbor