



## VDI multiple toolholder, Shank $\varnothing$ d1: 50mm



### Order data

Order number	319185 50
GTIN	4045197955067
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

#### Standard:

DIN ISO 10889 / DIN 69880 / VDI 4325, Blatt 2.

### Technical description

Shank $\varnothing$ D <sub>1</sub>	50 mm
Colour code for VDI shanks	VDI 50
b <sub>1</sub>	105 mm
h <sub>5</sub>	35 mm
h <sub>1</sub>	32 mm
b <sub>2</sub>	50 mm
l <sub>1</sub>	85 mm
Shank width b <sub>3</sub>	25.5 mm

h <sub>2</sub>	41 mm
h <sub>6</sub>	60 mm
Type of product	VDI multiple toolholder