



## VDI multiple toolholder, overhead, Shank $\varnothing$ d1: 50mm



### Order data

Order number	319190 50
GTIN	4045197955098
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

#### Standard:

DIN ISO 10889 / DIN 69880 / VDI 4325, Blatt 2.

### Technical description

Shank width $b_3$	25.5 mm
Shank $\varnothing$ $D_1$	50 mm
Colour code for VDI shanks	VDI 50
$b_2$	50 mm
$h_6$	60 mm
$h_5$	35 mm
$h_2$	41 mm

$b_1$	105 mm
$h_1$	32 mm
$l_1$	85 mm
Type of product	VDI multiple toolholder