

**Malleable cast iron screw clamp, Jaw capacity: 800mm****Order data**

Order number	860000 800
GTIN	4008158011509
Item class	83J

Description**Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp.

Movable pressure pad from size 160 can be exchanged without tools. **Without protective cap.**

Clamping force of up to 7000 N.

Standard:

DIN 5117

Spare part:

Protective cap No. 860115.

Technical description

Throat	120 mm
Jaw capacity	800 mm
Cross section of the slide rail	35×11 mm

Type of product

Clamp

Accessories

Pair of Vario clamp attachments

862950

Complete lower section for Moment screw clamps Type 500

860060 500

Pressure plate assortment 8 pieces Pressure pad Ø 37 mm

860115 37