



Lightweight malleable cast iron screw clamp, Jaw capacity: 500mm



Order data

Order number	860200 500
GTIN	4008158014616
Item class	82C

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

Standard:

DIN 5117

Technical description

Cross section of the slide rail	29×9 mm
Throat	120 mm
Jaw capacity	500 mm
Type of product	Clamp