



## Malleable cast iron screw clamp, Jaw capacity: 600mm



### Order data

Order number	860100 600
GTIN	4008158012049
Item class	82C

### Description

#### Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

#### Standard:

**DIN 5117**

### Technical description

Throat	120 mm
Jaw capacity	600 mm
Cross section of the slide rail	35×11 mm
Type of product	Clamp

