

FLUKE®

**Current and voltage tester, Type: T6-600****Order data**

Order number	473215 T6-600
GTIN	095969854108
Item class	47H

**Description****Version:**

Open current clamp for **contactless measurement of voltage**, current and frequency, without measurement leads that create contact with live points. Exchangeable test prods. For measuring conductor cross-sections up to 120 mm<sup>2</sup>. Easy-to-read display with back lighting.

**Application:**

For professional voltage and polarity testing, and for current measurement. Suitable for working on electrical systems, industrial systems, maintenance and servicing (troubleshooting).

**Standard:**

**IEC / EN 61010-1; IEC / EN 61326; VDE 0843-20-1.**

**Supplied with:**

Supplied with 2 batteries 081561 size LR6, connected measurement leads with detachable 4 mm caps to protect the measuring tips.

**Technical description**

Article no of the battery / rechargeable battery fitted	081561 LR6
Measurement process	TRUE RMS
Number of batteries contained	2

Overvoltage category	CAT III 600 V
Calibration	I4
AC current	0.1 – 200 A
Resistance	1 $\Omega$ – 2 k $\Omega$
Data storage key	yes
Display range AC	1 - 600 V
Display range DC	1 - 600 V
Power supply	Battery-powered
Type of product	Multimeter

## Services

CalibrationClamp meter Type D	027050 D
-------------------------------	----------

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------