



Stock square of anodised aluminium Accuracy class 1, Stock length: 100X70mm



Order data

Order number	451050 100X70
GTIN	4067263117872
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Stock length	100×70 mm
Length of short arm	70 mm
Length of long arm	100 mm
Shank cross-section	100×70 mm
Right angle tolerance	0.015 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Stock square

Services

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750