

FLUKE.

Current and voltage tester, Type: T6-1000**Order data**

Order number	473215 T6-1000
GTIN	095969854030
Item class	47H

Description**Version:**

Open current clamp for **contactless measurement of voltage**, current and frequency, without measurement leads that create contact with live points. Exchangeable test prods. For measuring conductor cross-sections up to 120 mm². Easy-to-read display with back lighting. Simultaneous display of the actual voltage value and current value.

Application:

For professional voltage and polarity testing, and for current measurement. Suitable for working on electrical systems, industrial systems, maintenance and servicing (troubleshooting).

Standard:

IEC / EN 61010-1; IEC / EN 61326; VDE 0843-20-1.

Supplied with:

Supplied with 2 batteries 081561 size LR6, connected measurement leads with detachable 4 mm caps to protect the measuring tips.

Technical description

AC current	0.1 – 200 A
Article no of the battery / rechargeable battery fitted	081561 LR6

Calibration	I4
Resistance	1 Ω – 100 k Ω
Overvoltage category	CAT III 1000 V; CAT IV 600 V
Measurement process	TRUE RMS
Number of batteries contained	2
Data storage key	yes
Display range DC	1 - 1000 V
Display range AC	1 - 1000 V
Frequency measurement	45 - 66 Hz
Power supply	Battery-powered
Type of product	Multimeter

Services

CalibrationClamp meter Type D	027050 D
-------------------------------	----------

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------