



## Stock square of anodised aluminium Accuracy class 1, Stock length: 400X265mm



### Order data

Order number	451050 400X265
GTIN	4045197955739
Item class	42F

### Description

#### Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

### Technical description

Right angle tolerance	0.03 mm
Length of short arm	265 mm
Shank cross-section	45×10 mm
Stock length	400×265 mm
Length of long arm	400 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Stock square

### Services

CalibrationStock, try, and bevel edge squares maximum arm length 750 mm	025000 750
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750