



## Stock square of anodised aluminium Accuracy class 1, Stock length: 200X130mm



### Order data

Order number	451050 200X130
GTIN	4067263117896
Item class	42F

### Description

#### Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

### Technical description

Length of long arm	200 mm
Shank cross-section	30×7 mm
Stock length	200×130 mm
Length of short arm	130 mm
Right angle tolerance	0.02 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Stock square

### Services

DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	025010 750
Calibration Stock, try, and bevel edge squares maximum arm length 300 mm	025000 300