

**Try square of anodised aluminium Accuracy class 1, Stock length: 100X70mm****Order data**

Order number	451060 100X70
GTIN	4067263125945
Item class	42F

**Description****Version:**

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

**Technical description**

Stock length	100×70 mm
Right angle tolerance	0.015 mm
Shank cross-section	20×5 mm
Length of long arm	100 mm
Length of short arm	70 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

## Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100