



Try square of anodised aluminium Accuracy class 1, Stock length: 300X200mm



Order data

Order number	451060 300X200
GTIN	4067263125983
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Length of short arm	200 mm
Length of long arm	300 mm
Shank cross-section	40×8 mm
Right angle tolerance	0.025 mm
Stock length	300×200 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750