



Try square of anodised aluminium Accuracy class 1, Stock length: 150X100mm



Order data

Order number	451060 150X100
GTIN	4067263125952
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Shank cross-section	30×6 mm
Length of long arm	150 mm
Right angle tolerance	0.018 mm
Length of short arm	100 mm
Stock length	150×100 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300