



Try square of anodised aluminium Accuracy class 1, Stock length: 75X50mm



Order data

Order number	451060 75X50
GTIN	4067263125938
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Length of long arm	75 mm
Stock length	75x50 mm
Length of short arm	50 mm
Shank cross-section	15x4 mm
Right angle tolerance	0.014 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

Services

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750