



Try square of anodised aluminium Accuracy class 1, Stock length: 400X265mm



Order data

Order number	451060 400X265
GTIN	4067263125990
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Shank cross-section	45×10 mm
Length of long arm	400 mm
Right angle tolerance	0.03 mm
Stock length	400×265 mm
Length of short arm	265 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 750 mm	025000 750