



Try square of anodised aluminium Accuracy class 1, Stock length: 500X330mm



Order data

Order number	451060 500X330
GTIN	4045197955869
Item class	42F

Description

Version:

Square of hardened aluminium (HRC 63). Corrosion-resistant. Non-magnetic. Scratch-resistant, black anodised non-dazzle surface. Test faces precision finished. Clear laser-engraved scale.

Technical description

Length of short arm	330 mm
Right angle tolerance	0.035 mm
Length of long arm	500 mm
Shank cross-section	50×10 mm
Stock length	500×330 mm
Calibration	F1
Standard	Manufacturer's standard
Accuracy	1

Material	Aluminium
all parts	hardened
Test faces	milled
Type of product	Try squares

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 750 mm	025000 750