



One-hand clamp, Jaw capacity: 300mm



Order data

| | |
|--------------|---------------|
| Order number | 860250 300 |
| GTIN | 4008158030661 |
| Item class | 83K |

Description

Version:

Clamp body of quenched and tempered steel. Housing and lever of glass fibre reinforced polyamide. Flexible plastic protective covers for gentle clamping. **Fast clamping** of components **using only one hand** due to lever advance. Can be operated using the **2-component handle** or from the rail side. **Positive clamping** (and releasing) by means of trapezoidal thread spindle as with normal all-steel clamps. Ergonomic release button for easy slide bar movement. Clamping force up to 3500 N.

Application:

Universally useful, in particular, where the **user has only one hand free for clamping**, e.g. when holding strips, profiles, cables, pipes etc. Also advantageous for **overhead work** and **springy** or **yielding components**.

Technical description

| | |
|---------------------------------|-------------|
| Jaw capacity | 300 mm |
| Throat | 100 mm |
| Cross section of the slide rail | 19.5×9.5 mm |

| | |
|------------------------|---------|
| maximum clamping force | 3500 Nm |
| Type of product | Clamp |