



## Malleable cast iron screw clamp, Jaw capacity: 800mm



### Order data

Order number	860100 800
GTIN	4008158012063
Item class	82C

### Description

#### Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

#### Standard:

**DIN 5117**

### Technical description

Jaw capacity	800 mm
Throat	120 mm
Cross section of the slide rail	35×11 mm
Type of product	Clamp

