



## One-hand clamp, Jaw capacity: 600mm



### Order data

Order number	860250 600
GTIN	4008158030692
Item class	83K

### Description

#### Version:

Clamp body of quenched and tempered steel. Housing and lever of glass fibre reinforced polyamide. Flexible plastic protective covers for gentle clamping. **Fast clamping** of components **using only one hand** due to lever advance. Can be operated using the **2-component handle** or from the rail side. **Positive clamping** (and releasing) by means of trapezoidal thread spindle as with normal all-steel clamps. Ergonomic release button for easy slide bar movement. Clamping force up to 3500 N.

#### Application:

**Universally useful**, in particular, where the **user has only one hand free for clamping**, e.g. when holding strips, profiles, cables, pipes etc. Also advantageous for **overhead work** and **springy** or **yielding components**.

### Technical description

Jaw capacity	600 mm
Cross section of the slide rail	19.5×9.5 mm
Throat	100 mm

maximum clamping force	3500 Nm
Type of product	Clamp