



## Malleable cast iron screw clamp, Jaw capacity: 160mm



### Order data

Order number	860000 160
GTIN	4008158008677
Item class	83J

### Description

#### Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools. With plastic protective cover on the clamping jaw.

Clamping force of up to 6000 N.

#### Standard:

**DIN 5117**

#### Spare part:

Protective cap No. 860115.

### Technical description

Jaw capacity	160 mm
Throat	80 mm

Cross section of the slide rail	25×6 mm
Type of product	Clamp

---

## Accessories

Pair of Vario clamp attachments	862950
Pressure plate assortment 8 pieces Pressure pad Ø 27 mm	860115 27