



Vernier caliper, Måleområde: 1500 mm



Order data

Order number	415195 1500
GTIN	4045197956668
Item class	42A

Description

Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component Ø.** With locking screw. Offset and rounded jaw ends for internal measurements. With fine adjustment.

all parts: hardened

Standard: DIN 862

Reversible reading: mm / inch

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Error limit: 0.18 mm

Jaw length: 200 mm

Internal jaw Ø: 30 mm

Weight: 5.3 kg

Technical description

Reversible reading	mm / inch
Jaw length	200 mm
Measuring range	0 - 1500 mm
Scale divisions	0.05 mm
Internal jaw Ø	30 mm
Calibration	A1
Error limit	0.18 mm

Weight	5.3 kg
Graduation	1/20 mm
Standard	DIN 862
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 2000 mm	011030 2000
Labelling laser-etched Type	018940