



## Vernier caliper, Måleområde: 800 mm



### Order data

Order number	415195 800
GTIN	4045197956644
Item class	42A

### Description

#### Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component Ø.** With locking screw. Offset and rounded jaw ends for internal measurements.

all parts: hardened

Standard: DIN 862

Reversible reading: mm / inch

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Error limit: 0.1 mm

Jaw length: 150 mm

Internal jaw Ø: 20 mm

Weight: 2.1 kg

### Technical description

Measuring range	0 - 800 mm
Internal jaw Ø	20 mm
Reversible reading	mm / inch
Weight	2.1 kg
Jaw length	150 mm
Scale divisions	0.05 mm
Calibration	A1

Error limit	0.1 mm
Graduation	1/20 mm
Standard	DIN 862
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

### Services

Calibration Calipers / depth gauges maximum measuring range 1000 mm	011030 1000
DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm	011050 1000
Labelling laser-etched Type	018940