



Vernier caliper, Måleområde: 3000 mm



Order data

Order number	415195 3000
GTIN	4045197997302
Item class	42A

Description

Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component Ø.** With locking screw. Offset and rounded jaw ends for internal measurements. With fine adjustment.

all parts: hardened

Standard: Manufacturer's standard

Reversible reading: mm / inch

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Error limit: 0.64 mm

Jaw length: 200 mm

Internal jaw Ø: 50 mm

Weight: 19 kg

Technical description

Error limit	0.64 mm
Internal jaw Ø	50 mm
Scale divisions	0.05 mm
Graduation	1/20 mm
Jaw length	200 mm
Weight	19 kg
Measuring range	0 - 3000 mm

Reversible reading	mm / inch
Calibration	A1
Standard	Manufacturer's standard
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

Services

Calibration Calipers / depth gauges maximum measuring range 3000 mm	011030 3000
Labelling laser-etched Type	018940