

**Malleable cast iron screw clamp, Jaw capacity: 1000mm****Order data**

Order number	860100 1000
GTIN	4008158011875
Item class	82C

**Description****Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

**Standard:**

**DIN 5117**

**Technical description**

Jaw capacity	1000 mm
Cross section of the slide rail	35×11 mm
Throat	120 mm
Type of product	Clamp

