

**Geared clamp, Jaw capacity: 300mm****Order data**

Order number	860271 300
GTIN	4008158040813
Item class	83K

**Description****Version:**

Ergonomically shaped 2-component plastic handle, burnished rail of drawn steel. Fibreglass-reinforced plastic body, smooth-running spindle with trapezoidal thread and tiltable pressure pad. With release handle for quick adjustment.

**Application:**

Enormously flexible and suitable for use even in the tightest spaces, for clamping forces up to 2000N.

**Technical description**

Jaw capacity	300 mm
Throat	60 mm
Cross section of the slide rail	19×6 mm
maximum clamping force	2000 Nm
Type of product	Clamp

