



One-hand clamp, reversible, Jaw capacity: 160mm



Order data

Order number	860280 160
GTIN	4008158028521
Item class	83K

Description

Version:

Rails of drawn steel, burnished. Sliding jaw, fixed jaw, body, and pump handle of glass fibre reinforced polyamide (unbreakable). Large flat clamping faces permit clamping all round the rail. Handy **rotary button** for quick **change-over** from clamping to spreading. With release handle for quick adjustment.

Application:

For general purpose use, easy to use one-handed for low clamping pressures (up to 1200 N).

Clamping and spreading with quick change-over.

Technical description

Throat	85 mm
Spreading width	75 - 235 mm
Jaw capacity	160 mm
Cross section of the slide rail	20×5 mm
maximum clamping force	1200 Nm

Type of product

Clamp