



## Self-levelling cross-hair laser LINO, Type: L2P5



### Order data

Order number	468481 L2P5
GTIN	7640110697542
Item class	47C

### Description

#### Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. Pulse function with power-saving mode. **Very long working life** of up to 44 h due to Li-ion battery. The magnetic adapter can be attached to any wall that has steel elements. **The magnet can be freely pivoted and easily released.** Locking for inclined projections and for protection in transport. Additional horizontal and vertical (plumb) laser lines

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with adapter, Li-ion battery, charger, battery holder, target board and case.

IP Index of Protection: IP 54

Error limit: 0.2 mm/m

Laser class: 2

Colour of the laser: red

Range: 25 m

Range with receiver: 80 m

Levelling range:  $\pm 4$  degrees

## Technical description

Range	25 m
Depth	100 mm
Error limit	0.2 mm/m
Levelling range	±4 degrees
Range with receiver	80 m
Threaded socket for stand	1/4 UNC inch
Width	60 mm
IP Index of Protection	IP 54
Height	110 mm
Weight	530 g
Laser class	2
Colour of the laser	red
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Type of product	Self-levelling cross-hair laser

## Accessories

Alkaline-manganese batteries International size LR6	081556 LR6
Alkaline-manganese batteries International size LR6	081561 LR6