



Self-levelling cross-hair laser LINO, Type: L2P5G



Order data

Order number	468481 L2P5G
GTIN	7640110697559
Item class	47C

Description

Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. Pulse function with power-saving mode. **Very long working life** of up to 44 h due to Li-ion battery. The magnetic adapter can be attached to any wall that has steel elements. **The magnet can be freely pivoted and easily released.** Locking for inclined projections and for protection in transport. Additional horizontal and vertical (plumb) laser lines

With green laser lines for optimum visibility. Up to 400% better visibility than red laser lines.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with adapter, Li-ion battery, charger, battery holder, target board and case.

IP Index of Protection: IP 54

Error limit: 0.2 mm/m

Laser class: 2

Colour of the laser: green

Range: 35 m

Range with receiver: 80 m

Levelling range: ± 4 degrees

Technical description

Range with receiver	80 m
IP Index of Protection	IP 54
Levelling range	±4 degrees
Depth	100 mm
Error limit	0.2 mm/m
Height	110 mm
Width	60 mm
Range	35 m
Threaded socket for stand	1/4 UNC inch
Weight	530 g
Laser class	2
Colour of the laser	green
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Type of product	Self-levelling cross-hair laser

Accessories

Alkaline-manganese batteries International size LR6	081556 LR6
Alkaline-manganese batteries International size LR6	081561 LR6