



Malleable cast iron screw clamp, Jaw capacity: 200mm



Order data

Order number	860000 200
GTIN	4008158008707
Item class	83J

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools. With plastic protective cover on the clamping jaw.

Clamping force of up to 6000 N.

Standard:

DIN 5117

Spare part:

Protective cap No. 860115.

Technical description

Jaw capacity	200 mm
Throat	100 mm

Cross section of the slide rail	27×7 mm
Type of product	Clamp

Accessories

Pair of Vario clamp attachments	862950
Pressure plate assortment 8 pieces Pressure pad Ø 30 mm	860115 30