

Garant**Components for mobile drawer cabinets Direction of pushing from the side wall, Type: R27E****Order data**

Order number	942948 R27E
GTIN	4045197526373
Item class	91H

Description**Version:**

Pair of wheeled subframes - each consisting of 2 ball-bearing mounted wheels linked by a transverse subframe; one subframe with fixed wheels, the other with castors; wheel Ø 100 mm, with parking brake. **Note the movement direction of the wheels.** Load capacity 600 kg evenly distributed.

Suitable for:

Pair of wheeled subframes suitable for mobile tool cabinets of product group 94 (up to 08/2019) with **dimensions 36x27 units** and **54x27 units**. For reasons of safety (risk of tipping over) the maximum usable height of the body is limited to 900 mm. **Push the cabinet from the side.**

Note:

- **Drawers in mobile tool cabinets must be fitted with individual drawer locking. This locks the drawer automatically on closing, so that it cannot open during transport. Individual drawer locking for drawers in product group 94 (up to 08/2019) can be found under No. 949605 in the spare parts list.**
- **When checking that the load capacity of the wheels (600 kg) is not exceeded, please make allowance for the tare weight of the cabinet itself.**
- **Please note the desired direction of movement of the wheels.**

Technical description

Type	R27E
------	------

Number of castors with parking brake	2
Number of castors without parking brake	2
Fixed wheel Ø	100 mm
Castor Ø	100 mm
total maximum load capacity	600 kg
Direction of running	Direction cabinet depth
Type of product	Handle