



Malleable cast iron screw clamp, Jaw capacity: 1250mm



Order data

Order number	860100 1250
GTIN	4008158011905
Item class	82C

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

Standard:

DIN 5117

Technical description

Cross section of the slide rail	35×11 mm
Throat	120 mm
Jaw capacity	1250 mm
Type of product	Clamp

