



Malleable cast iron screw clamp, Jaw capacity: 250mm



Order data

Order number	860000 250
GTIN	4008158008769
Item class	83J

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools. With plastic protective cover on the clamping jaw.

Clamping force of up to 6000 N.

Standard:

DIN 5117

Spare part:

Protective cap No. 860115.

Technical description

Cross section of the slide rail	29×9 mm
Throat	120 mm

Jaw capacity	250 mm
Type of product	Clamp

Accessories

Pressure plate assortment 8 pieces Pressure pad Ø 30 mm	860115 30
Pair of Vario clamp attachments	862950