



Malleable cast iron screw clamp, Jaw capacity: 2500mm



Order data

| | |
|--------------|---------------|
| Order number | 860000 2500 |
| GTIN | 4008158011318 |
| Item class | 83J |

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp. Movable pressure pad from size 160 can be exchanged without tools. **Without protective cap.** Clamping force of up to 7000 N.

Standard:

DIN 5117

Spare part:

Protective cap No. 860115.

Technical description

| | |
|---------------------------------|----------|
| Jaw capacity | 2500 mm |
| Cross section of the slide rail | 35×11 mm |
| Throat | 120 mm |

Type of product

Clamp

Accessories

Complete lower section for Moment screw clamps Type 500

860060 500

Pair of Vario clamp attachments

862950

Pressure plate assortment 8 pieces Pressure pad Ø 37 mm

860115 37