

**Malleable cast iron screw clamp, Jaw capacity: 160mm****Order data**

Order number	860100 160
GTIN	4008158004136
Item class	82C

**Description****Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. With plastic protective cover on the clamping jaw.

**Standard:****DIN 5117****Technical description**

Cross section of the slide rail	25×6 mm
Jaw capacity	160 mm
Throat	80 mm
Type of product	Clamp

