



Malleable cast iron screw clamp, Jaw capacity: 1500mm



Order data

Order number	860100 1500
GTIN	4008158011936
Item class	82C

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

Standard:

DIN 5117

Technical description

Jaw capacity	1500 mm
Throat	120 mm
Cross section of the slide rail	35×11 mm
Type of product	Clamp

