



Malleable cast iron screw clamp, Jaw capacity: 2000mm



Order data

| | |
|--------------|---------------|
| Order number | 860100 2000 |
| GTIN | 4008158011943 |
| Item class | 82C |

Description

Version:

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. **Without protective cap.**

Standard:

DIN 5117

Technical description

| | |
|---------------------------------|----------|
| Jaw capacity | 2000 mm |
| Cross section of the slide rail | 35×11 mm |
| Throat | 120 mm |
| Type of product | Clamp |

