



## Pneumatic random orbital sander, Type: 59043



### Order data

Order number	079656 59043
GTIN	616026590434
Item class	03R

### Description

#### Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level. Dynorbital spirit orbital sander (152 mm) for central extraction. For **fine sanding** with a 2.5 mm orbital stroke. **Integral extraction** via a hose and dust bag supplied including hook and loop pad No. 567872 size 150.

#### Supplied with:

Including the necessary coupling adaptors.

#### Note:

See No. 567775 or 567901 for hook and loop grinding discs.

DynaMaze hook and loop backing pad for No. 079655 and 079656 size X61V and size 58436 can be found under No. 567872 size 150.

### Technical description

Type of extraction	Own dust extraction
Operating noise	77 dB(A)
Weight	0.6 kg
Backing pad Ø	150 mm

maximum speed	12000 min <sup>-1</sup>
maximum vibration to EN	<2.5 m/s <sup>2</sup>
maximum air consumption	396 l/min
Manufacturer's designation	Dynaorbital 152 mm
Stroke	2.5 mm
Type of product	Orbital sander

## Accessories

Paper velour-backed abrasive disc (A)6 + 1 holes Grit 320	567775 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 800	567775 800
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 240	567775 240
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 400	567775 400
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 180	567775 180
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 120	567775 120
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 40	567775 40
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 80	567775 80
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 600	567775 600
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 60	567775 60