

**Garant****Malleable cast iron screw clamp, Jaw capacity: 2000mm****Order data**

Order number	860050 2000
GTIN	4045197559739
Item class	81D

**Description****Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping.

Movable clamping arm **with anti-slip protection**, preventing inadvertent release of the clamp.

Movable pressure pad from size 160 can be exchanged without tools.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands. **Without protective cap.**

**Standard:****DIN 5117****Spare part:**

Protective cap No. 860051.

**Technical description**

Cross section of the slide rail	35×11 mm
---------------------------------	----------

Jaw capacity	2000 mm
Throat	120 mm
Type of product	Clamp

---

## Accessories

Pressure plate assortment 12 pieces Type 300-2500	860051 300-2500
---	-----------------