



LED-EX torch with batteries, Type: 4AA2B



Order data

Order number	081521 4AA2B
GTIN	032705146523
Item class	08C

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

High-performance LED lamps shock-resistant, dust-proof and waterproof.

With **LED reflector technology. LED hand lamp with primary and secondary light**, front beam for primary light (shines forwards), rotary head switch for secondary light (shines on the feet). No reduction in operating time when using both beams of light at the same time.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including 4xbatteries No. 081557 LR6.

Technical description

Battery type	Mignon, AA
IP Index of Protection	IP 67
Weight	153 g
Illumination	170 lm
Head Ø	35 mm
ATEX zone	zone 20
ATEX zone	Zone 0
Colour of housing	yellow

Number of batteries contained	4
Illumination time	6 h
Illumination step 2	20 lm
Overall length	158 mm
Tool properties	Suitable for EX areas
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR6	081551 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081552 LR6
Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081554 LR6