



## LED cordless work lamp, Power consumption: 17 W



### Order data

Order number	081254 17
GTIN	5708997354391
Item class	08C

### Description

#### Version:

Sturdy LED work lights with shock-resistant aluminium casing and rubber protective surround.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

**NOVA work lamps** with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

IP Index of Protection: IP 67

ATEX zone: no

Illumination: 150 - 1500 lm

CRI value: 80

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Overall length: 163 mm

### Technical description

Colour temperature	6000 K
Battery capacity	5.4 A·h

Battery voltage	3.7 V
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
ATEX zone	no
IP Index of Protection	IP 67
Illumination	150 - 1500 lm
Number of rechargeable batteries contained	1
Overall height	163 mm
Overall length	163 mm
Overall width	63 mm
CRI value	80
Weight	710 g

---

## Accessories

Three-leg stand Height 1,35-3 m	081252 1,35-3
---------------------------------	---------------