



## Safety hose reel, plastic casing Compressed air, Ø 8 ×12 mm, Type: 10S



### Order data

Order number	080072 10S
GTIN	7391390327154
Item class	08A

### Description

#### Version:

**Safety hose reel** with **hose guide** and powerful controlled retraction.

Impact resistant enclosed **plastic casing** for use in dirty and dusty environments. Compact design, easy to mount on the wall or ceiling, with **180° swivel angle**. **PU hose** suitable for high throughputs, with high abrasion resistance and steel compressed air connection fittings.

#### Note:

For coupling, see No. 080286.

### Technical description

SCS automatic roll-up drum	yes
Hose external Ø	12 mm
Hose internal Ø	8 mm
Material of hose	Polyurethane
Colour of housing	blue
Connection outlet	1/4 in
maximum operating pressure	16 bar
Connection inlet	1/4 in

Colour of hose	blue
Material of the housing	Plastic
usable hose length	10 m
Body width	406 mm
Body depth	190 mm
Body height	313 mm
suitable for	Compressed air
Product name attribute	Ø 8 ×12 mm
Type of product	Hose reel

---

## Accessories

Safety shut-offInternal thread Connection internal thread 3/8 in	080286 3/8
Safety shut-offInternal thread Connection internal thread 1/4 in	080286 1/4
Safety shut-offInternal thread Connection internal thread 1/2 in	080286 1/2