

**Safety hose reel, plastic casing Compressed air, Ø 8 ×12 mm, Type: 17S****Order data**

Order number	080072 17S
GTIN	7391390327246
Item class	08A

Description**Version:**

Safety hose reel with **hose guide** and powerful controlled retraction.

Impact resistant enclosed **plastic casing** for use in dirty and dusty environments. Compact design, easy to mount on the wall or ceiling, with **180° swivel angle**. **PU hose** suitable for high throughputs, with high abrasion resistance and steel compressed air connection fittings.

Note:

For coupling, see No. 080286.

Technical description

Material of the housing	Plastic
usable hose length	17 m
Material of hose	Polyurethane
Connection outlet	1/4 in
Connection inlet	1/4 in
Colour of hose	blue
maximum operating pressure	16 bar
SCS automatic roll-up drum	yes

Hose internal Ø	8 mm
Hose external Ø	12 mm
Colour of housing	blue
Body depth	190 mm
Body height	409 mm
Body width	490 mm
suitable for	Compressed air
Product name attribute	Ø 8 × 12 mm
Type of product	Hose reel

Accessories

Safety shut-off Internal thread 1/2 in	Connection internal thread 080286 1/2
Safety shut-off Internal thread 3/8 in	Connection internal thread 080286 3/8
Safety shut-off Internal thread 1/4 in	Connection internal thread 080286 1/4