

**Safety hose reel, plastic casing Compressed air, Ø 11 ×16 mm, Type: 10S****Order data**

Order number	080077 10S
GTIN	7391390327383
Item class	08A

Description**Version:**

Safety hose reel with **hose guide** and powerful controlled retraction.

Impact resistant enclosed **plastic casing** for use in dirty and dusty environments. Compact design, easy to mount on the wall or ceiling, with **180° swing angle**. **PU hose** suitable for high throughputs, with high abrasion resistance and steel compressed air connection fittings.

Note:

For coupling, see No. 080286.

Technical description

maximum operating pressure	12 bar
Hose internal Ø	11 mm
usable hose length	10 m
Material of hose	Polyurethane
Connection inlet	1/2 in
Connection outlet	1/2 in
Colour of housing	blue
SCS automatic roll-up drum	yes

Hose external Ø	16 mm
Colour of hose	blue
Material of the housing	Plastic
Body height	409 mm
Body width	490 mm
Body depth	190 mm
suitable for	Compressed air
Product name attribute	Ø 11 ×16 mm
Type of product	Hose reel

Accessories

Safety shut-offInternal thread Connection internal thread 3/8 in	080286 3/8
Safety shut-offInternal thread Connection internal thread 1/4 in	080286 1/4
Safety shut-offInternal thread Connection internal thread 1/2 in	080286 1/2