

STABILA **Light metal spirit level with magnet, Length: 400mm****Order data**

Order number	467220 400
GTIN	4005069191771
Item class	46M

**Description****Version:**

Body of rectangular profile. Unbreakable Perspex vials. Specially corrosion-resistant light metal alloy.

Ribbed rectangular profile with two measuring faces. End caps of rubber prevent slipping when marking out. With **powerful magnets**.

**Technical description**

Number of vertical vials	1
Through grip	no
Length	400 mm
Error limit for overhead measurement	0.75 mm/m
Error limit in normal position	0.5 mm/m
Number of horizontal vials	1
Magnet	Permanent magnet
Material of the housing	Light metal alloy
Type of product	Spirit level