

STABILA **Light metal spirit level with magnet, Length: 600mm****Order data**

Order number	467220 600
GTIN	4005069191788
Item class	46M

Description**Version:**

Body of rectangular profile. Unbreakable Perspex vials. Specially corrosion-resistant light metal alloy.

Ribbed rectangular profile with two measuring faces. End caps of rubber prevent slipping when marking out. With **powerful magnets**.

Technical description

Error limit in normal position	0.5 mm/m
Number of vertical vials	1
Number of horizontal vials	1
Through grip	no
Error limit for overhead measurement	0.75 mm/m
Length	600 mm
Magnet	Permanent magnet
Material of the housing	Light metal alloy
Type of product	Spirit level