

STABILA 

Light metal spirit level with magnet, Length: 800mm



Order data

Order number	467220 800
GTIN	4005069191795
Item class	46M

Description

Version:

Body of rectangular profile. Unbreakable Perspex vials. Specially corrosion-resistant light metal alloy.

Ribbed rectangular profile with two measuring faces. End caps of rubber prevent slipping when marking out. With **powerful magnets**.

Technical description

Number of vertical vials	1
Through grip	no
Length	800 mm
Number of horizontal vials	1
Error limit in normal position	0.5 mm/m
Error limit for overhead measurement	0.75 mm/m
Magnet	Permanent magnet
Material of the housing	Light metal alloy
Type of product	Spirit level