

**Quick-change tapping chuck M3 – M12, Shank Ø d: 40mm****Order data**

Order number	319445 40
GTIN	4045197959669
Item class	32P

Description**Version:**

Resilient length compensation, smooth action due to ball bearing sleeve.

Standard:

DIN ISO 10889 / DIN 69880 und **VDI 3425**, Blatt 2.

Optional extras:

Quick-change tapping collets No. 335420 – 335620.

Technical description

Shank Ø D ₁	40 mm
Colour code for VDI shanks	VDI 40
Overhang L	61.5 mm
Length compensation by compression	7 mm
Length compensation by tension	7 mm
Chuck outside Ø D	38 mm
Type of product	VDI tapping chuck

