



## Quick-change tapping chuck M3 – M12, Shank Ø d: 30mm



### Order data

Order number	319445 30
GTIN	4045197959652
Item class	32P

### Description

#### Version:

Resilient length compensation, smooth action due to ball bearing sleeve.

#### Standard:

**DIN ISO 10889 / DIN 69880** und **VDI 3425**, Blatt 2.

#### Optional extras:

**Quick-change tapping collets** No. 335420 – 335620.

### Technical description

Shank Ø D <sub>1</sub>	30 mm
Colour code for VDI shanks	VDI 30
Overhang L	61.5 mm
Length compensation by compression	7 mm
Length compensation by tension	7 mm
Chuck outside Ø D	38 mm
Type of product	VDI tapping chuck

