

**Quick-change tapping chuck M6 – M20, Shank Ø d: 40mm****Order data**

Order number	319447 40
GTIN	4045197959683
Item class	32P

**Description****Version:**

Resilient length compensation, smooth action due to ball bearing sleeve.

**Standard:**

**DIN ISO 10889 / DIN 69880** und **VDI 3425**, Blatt 2.

**Optional extras:**

**Quick-change tapping collets** No. 335420 – 335620.

**Technical description**

Colour code for VDI shanks	VDI 40
Shank Ø D <sub>1</sub>	40 mm
Overhang L	86 mm
Length compensation by compression	12 mm
Length compensation by tension	12 mm
Chuck outside Ø D	54 mm
Type of product	VDI tapping chuck

